

64581055 Cut Sheet



WERMA siren element, 80-100 dB at 1m, 2.5 kHz tone frequency, self-adjusting pulse tone(s), 24 VDC, ABS/polycarbonate housing, black, IP65. For use with WERMA 70mm stack light elements.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/64581055>

Technical Specifications

Brand	WERMA
Item	Siren element
Loudness Decibel	80-100 dB at 1m
Tone Frequency	2.5 kHz
Tone Type	Self-adjusting pulse
Touch to Acknowledge	No
Voltage Rating	24 VDC
Housing Material	ABS/polycarbonate
Color	Black
IP Rating	IP65
For Use With	WERMA 70mm stack light elements

Agency Approvals

UL Listed File #	E164155
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/64581055.pdf>
See store item page for other formats.