

64585055 Cut Sheet



WERMA siren element, 100 dB at 1m, 1.6 kHz to 3.4 kHz tone frequency, (7) selectable tone(s), 24 VDC, polycarbonate housing, black, IP65. For use with WERMA 70mm stack light elements.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/64585055>

Technical Specifications

Brand	WERMA
Item	Siren element
Loudness Decibel	100 dB at 1m
Tone Frequency	1.6 kHz to 3.4 kHz
Tone Type	(7) selectable
Touch to Acknowledge	No
Voltage Rating	24 VDC
Housing Material	Polycarbonate
Color	Black
IP Rating	IP65
For Use With	WERMA 70mm stack light elements

Agency Approvals

UL Listed File #	E164155
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document