

64585055 Cut Sheet



WERMA siren element, 100 dB at 1m, 1.6 kHz to 3.4 kHz tone frequency, (7) selectable tone(s), 24 VDC, polycarbonate housing, black, IP65. For use with WERMA 70mm stack light elements.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/64585055>

Technical Specifications

| | |
|-----------------------------|---------------------------------|
| Brand | WERMA |
| Item | Siren element |
| Loudness Decibel | 100 dB at 1m |
| Tone Frequency | 1.6 kHz to 3.4 kHz |
| Tone Type | (7) selectable |
| Touch to Acknowledge | No |
| Voltage Rating | 24 VDC |
| Housing Material | Polycarbonate |
| Color | Black |
| IP Rating | IP65 |
| For Use With | WERMA 70mm stack light elements |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E164155 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/64585055.pdf>
See store item page for other formats.