

64924004 Cut Sheet



WERMA LED signal tower, (2) tiers, 70mm diameter, red/green, permanent light function, 24 VAC/VDC, colored lens, 154.2mm body length, black, 360 degree viewing angle, bracket mount, IP65.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/64924004>

Technical Specifications

Brand	WERMA
Item	Signal tower
Bulb Type	LED
Number Of Tiers	2
Diameter	70mm
Light Color(s)	Red/green
Light Function	Permanent
Voltage Rating	24 VAC/VDC
Lens Type	Colored
Body Length	154.2mm
Body Color	Black
Body Material	Polycarbonate
Tower Viewing Angle	360 degree
Connector Type	Pigtail
Mounting	Bracket
IP Rating	IP65

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document