

# 65730055 Cut Sheet



WERMA eSIGN series LED signal tower, white, (9) tiers, 72mm diameter, custom programmable colors, selectable multi light function, (10) selectable tone(s), 24 VDC, 360 degree viewing angle, 8-pin M12 A-coded, base or tube mount, IP66 and IP69K.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/65730055>

## Technical Specifications

<b>Brand</b>	WERMA
<b>Item</b>	Signal tower
<b>Bulb Type</b>	LED
<b>Series</b>	ESIGN
<b>Number of Pre-Assembled Tiers</b>	9
<b>Diameter</b>	72mm
<b>Light Color(s)</b>	Custom programmable colors
<b>Light Function</b>	Selectable permanent, blinking, flashing, double flash, triple flash or rotating
<b>Number of Alarms</b>	10
<b>Loudness Decibel</b>	105 dB at 1m
<b>Tone Frequency</b>	900 Hz to 3.6 kHz

<b>Tone Type</b>	(10) selectable
<b>Communication Port and Connection Type(s)</b>	(1) USB C
<b>Voltage Rating</b>	24 VDC
<b>Lens Type</b>	Clear
<b>Body Length</b>	271mm
<b>Body Color</b>	White
<b>Body Material</b>	Polycarbonate
<b>Tower Viewing Angle</b>	360 degree
<b>Connector Type</b>	8-pin M12 A-coded
<b>Mounting</b>	Base or tube
<b>IP Rating</b>	IP66 and IP69K

## Agency Approvals

<b>UL Listed File #</b>	E164155
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">Clean Room Certification ISO 14644-14</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/65730055.pdf>  
See store item page for other formats.