

65760055 Cut Sheet



WERMA eSIGN series LED signal tower, black, (15) tiers, 72mm diameter, custom programmable colors, selectable multi light function, (10) selectable tone(s), 24 VDC, 360 degree viewing angle, 8-pin M12 A-coded, base or tube mount, IP66 and IP69K.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/65760055>

Technical Specifications

Brand	WERMA
Item	Signal tower
Bulb Type	LED
Series	ESIGN
Number of Pre-Assembled Tiers	15
Diameter	72mm
Light Color(s)	Custom programmable colors
Light Function	Selectable permanent, blinking, flashing, double flash, triple flash or rotating
Number of Alarms	10
Loudness Decibel	105 dB at 1m
Tone Frequency	900 Hz to 3.6 kHz

Tone Type	(10) selectable
Communication Port and Connection Type(s)	(1) USB C
Voltage Rating	24 VDC
Lens Type	Clear
Body Length	372mm
Body Color	Black
Body Material	Polycarbonate
Tower Viewing Angle	360 degree
Connector Type	8-pin M12 A-coded
Mounting	Base or tube
IP Rating	IP66 and IP69K

Agency Approvals

UL Listed File #	E164155
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	Clean Room Certification ISO 14644-14

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/65760055.pdf>
See store item page for other formats.