

66212 Cut Sheet



Hallex fitting, liquid-tight, malleable iron, straight, 1-1/4in trade size, compression conduit connection, zinc electro-plated finish. Package of 2. For use with LFMC and NM-Type B electrical conduit. Sealing washer and locknut included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/66212>

Technical Specifications

Brand	Hallex
Item	Fitting
Liquid-tight	Yes
Fitting Type	Straight
Material	Malleable iron
Trade Size	1-1/4in
Conduit Connection Method	Compression
Box Connection Type	2-1/4in male NPT
Insulation	No
Finish	Zinc electro-plated

Knockout Size	2-1/4in
Liquid-tight Non-metallic Conduit Type B (NM) Trade Size	1-1/4in
Liquid-tight Flexible Metal Conduit (LFMC) Trade Size	1-1/4in
Quantity per Pack	2
For Use With	LFMC and NM-Type B electrical conduit
Includes	Sealing washer and locknut
Applicable Standards	UL 514B Listed

Agency Approvals

UL Listed File #	E30248
RoHS Status	No
EU REACH	View EU REACH document