

664X63D Cut Sheet



Bryant manual motor controller, enclosed, 60A, 600 VAC, 3-pole, 30hp, wall mount, thermoplastic housing, NEMA 4X, UL 508 rated.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/664X63D>

Technical Specifications

Brand	Bryant
Item	Manual motor controller
Body Type	Enclosed
Amperage Rating	60A
Voltage Rating	600 VAC
Number of Poles	3
Horsepower Rating	30hp
Mounting	Wall
Handle Type	Red/yellow handle
Housing Material	Thermoplastic
Housing Rating	NEMA 4X
Wiring Type	Installer determined wire entry, no pre-drilled openings or knockouts
Includes	NEMA 4X enclosure, (1) neutral bus connector and 66063D rotary controller
Application	Ideal for use in heavy wash-down and corrosive environments
UL Rating	UL 508 rated
Additional Information	Lockout/tagout capable. Chemical and impact resistant. Suitable as motor disconnect

Agency Approvals

UL Listed File #	E70402
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	46186
RoHS Status	No
EU REACH	View EU REACH document