

664X63D Cut Sheet



Bryant manual motor controller, enclosed, 60A, 600 VAC, 3-pole, 30hp, wall mount, thermoplastic housing, NEMA 4X, UL 508 rated.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/664X63D>

Technical Specifications

| | |
|-------------------|-------------------------|
| Brand | Bryant |
| Item | Manual motor controller |
| Body Type | Enclosed |
| Amperage Rating | 60A |
| Voltage Rating | 600 VAC |
| Number of Poles | 3 |
| Horsepower Rating | 30hp |
| Mounting | Wall |
| Handle Type | Red/yellow handle |
| Housing Material | Thermoplastic |

| | |
|------------------------|---|
| Housing Rating | NEMA 4X |
| Wiring Type | Installer determined wire entry, no pre-drilled openings or knockouts |
| Includes | NEMA 4X enclosure, (1) neutral bus connector and 66063D rotary controller |
| Application | Ideal for use in heavy wash-down and corrosive environments |
| UL Rating | UL 508 rated |
| Additional Information | Lockout/tagout capable. Chemical and impact resistant. Suitable as motor disconnect |

Agency Approvals

| | |
|----------------------|------------------------|
| UL Listed File # | E70402 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | 46186 |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/664X63D.pdf>
See store item page for other formats.