

66905B Cut Sheet



Halex fitting, liquid-tight, malleable iron, 90-degree, 1/2in trade size, compression conduit connection, zinc electro-plated finish. Package of 10. For use with LFMC and NM-Type B electrical conduit. Sealing washer and locknut included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/66905B>

Technical Specifications

Brand	Halex
Item	Fitting
Liquid-tight	Yes
Fitting Type	90-degree
Material	Malleable iron
Trade Size	1/2in
Conduit Connection Method	Compression
Box Connection Type	1/2in male NPT
Insulation	No
Finish	Zinc electro-plated

Knockout Size	1/2in
Liquid-tight Non-metallic Conduit Type B (NM) Trade Size	1/2in
Liquid-tight Flexible Metal Conduit (LFMC) Trade Size	1/2in
Quantity per Pack	10
For Use With	LFMC and NM-Type B electrical conduit
Includes	Sealing washer and locknut
Applicable Standards	UL 514B Listed

Agency Approvals

UL Listed File #	E30248
CE	None
RoHS Status	No
EU REACH	View EU REACH document