

68360 Cut Sheet



Viking jobber-length drill bit set, 21 pieces, 8% cobalt high-speed steel (HSSE-Co8), round shank, imperial, gold oxide finish, metal index case.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/68360>

Technical Specifications

| | |
|------------------|--|
| Brand | Viking |
| Item | Drill bit set |
| Number of Pieces | 21 |
| Material | 8% cobalt high-speed steel (HSSE-Co8) |
| Drill Bit Type | Jobber-length |
| Drill Bit Size | 1/16in, 5/64in, 3/32in, 7/64in, 1/8in, 9/64in, 5/32in, 11/64in, 3/16in, 13/64in, 7/32in, 15/64in, 1/4in, 17/64in, 9/32in, 19/64in, 5/16in, 21/64in, 11/32in, 23/64in and 3/8in |
| Finish | Gold oxide |
| Point Angle | 135 degrees |
| Point Cut | Split |

| | |
|------------------|--|
| Shank Type | Round |
| Application | Hole cutting |
| For Use On | Steel, stainless steel, titanium alloys and abrasives |
| Measurement Type | Imperial |
| Package Type | Metal index case |
| Set Includes | Includes (21) jobber-length drill bits (1/16in, 5/64in, 3/32in, 7/64in, 1/8in, 9/64in, 5/32in, 11/64in, 3/16in, 13/64in, 7/32in, 15/64in, 1/4in, 17/64in, 9/32in, 19/64in, 5/16in, 21/64in, 11/32in, 23/64in, 3/8in), durable metal case |

Agency Approvals

| | |
|----------------------|---|
| UL Listed File # | N/A |
| UL Recognized File # | N/A |
| UL Hazardous File # | N/A |
| CE | None |
| CSA File # | N/A |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |