

68410 Cut Sheet



Viking jobber-length drill bit set, 29 pieces, 8% cobalt high-speed steel (HSSE-Co8), round shank, imperial, gold oxide finish, ultra-dex carrying case.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/68410>

Technical Specifications

Brand	Viking
Item	Drill bit set
Number of Pieces	29
Material	8% cobalt high-speed steel (HSSE-Co8)
Drill Bit Type	Jobber-length
Drill Bit Size	1/16in, 5/64in, 3/32in, 7/64in, 1/8in, 9/64in, 5/32in, 11/64in, 3/16in, 13/64in, 7/32in, 15/64in, 1/4in, 17/64in, 9/32in, 19/64in, 5/16in, 21/64in, 11/32in, 23/64in, 3/8in, 25/64in, 13/32in, 27/64in, 7/16in, 29/64in, 15/32in, 31/64in and 1/2in
Finish	Gold oxide
Point Angle	135 degrees
Point Cut	Split

Shank Type	Round
Application	Hole cutting
For Use On	Steel, stainless steel, titanium alloys and abrasives
Measurement Type	Imperial
Package Type	Ultra-dex carrying case
Set Includes	Includes (29) jobber-length drill bits (1/16in, 5/64in, 3/32in, 7/64in, 1/8in, 9/64in, 5/32in, 11/64in, 3/16in, 13/64in, 7/32in, 15/64in, 1/4in, 17/64in, 9/32in, 19/64in, 5/16in, 21/64in, 11/32in, 23/64in, 3/8in, 25/64in, 13/32in, 27/64in, 7/16in, 29/64in, 15/32in, 31/64in, 1/2in), ultra-dex carrying case

Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement