

68534 Cut Sheet



Viking step drill bit, 1/4in to 1in, size #2, 8 steps, split point, high-speed steel (HSS), Titanium-Nitride (TiN) coated finish, 1/4in hex shank, 3in (76mm) overall length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/68534>

Technical Specifications

| | |
|----------------------|--|
| Brand | Viking |
| Item | Drill bit |
| Replacement | No |
| Drill Bit Type | Step |
| Size | 1/4in, 5/16in, 3/8in, 7/16in, 1/2in, 9/16in, 5/8in, 11/16in, 3/4in, 13/16in, 7/8in and 1in |
| Step Drill Size | #2 |
| Number Of Hole Sizes | 8 |

| | |
|----------------|--|
| Material | High-speed steel (HSS) |
| Finish | Titanium-Nitride (TiN) coated |
| Point Cut | Split |
| Shank Type | 1/4in hex |
| Overall Length | 3in (76mm) |
| For Use On | Steel, brass, plastic, stainless steel, bronze, cast iron and aluminum |
| Application | Hole cutting |

Agency Approvals

| | |
|----------------------|---|
| UL Listed File # | N/A |
| UL Recognized File # | N/A |
| UL Hazardous File # | N/A |
| CE | None |
| CSA File # | N/A |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |