

# 68581 Cut Sheet



Viking step drill bit set, 3 pieces, high-speed steel (HSS), 1/4in hex shank, size #1, #8 and #11, imperial, Titanium-Nitride (TiN) coated finish, plastic case.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/68581>

## Technical Specifications

<b>Brand</b>	Viking
<b>Item</b>	Drill bit set
<b>Number of Pieces</b>	3
<b>Material</b>	High-speed steel (HSS)
<b>Drill Bit Type</b>	Step
<b>Drill Bit Size</b>	1/8in, 5/32in, 3/16in, 7/32in, 1/4in, 9/32in, 5/16in, 11/32in, 3/8in, 13/32in, 7/16in, 15/32in, 1/2in, 9/16in, 5/8in, 11/16in, 3/4in, 13/16in, 7/8in and 1-1/8in
<b>Step Drill Size</b>	#1, #8 and #11
<b>Number Of Hole Sizes</b>	13, 12 and 2
<b>Finish</b>	Titanium-Nitride (TiN) coated

<b>Point Cut</b>	Split
<b>Shank Type</b>	1/4in hex
<b>Application</b>	Hole cutting
<b>For Use On</b>	Steel, brass, plastic, stainless steel, bronze, cast iron and aluminum
<b>Measurement Type</b>	Imperial
<b>Package Type</b>	Plastic case
<b>Set Includes</b>	Includes (1) #1 13 step drill bit (1/8in, 5/32in, 3/16in, 7/32in, 1/4in, 9/32in, 5/16in, 11/32in, 3/8in, 13/32in, 7/16in, 15/32in, 1/2in), (1) #11 2 step drill bit (7/8in, 1-1/8in), plastic carrying case

## Agency Approvals

<b>UL Listed File #</b>	N/A
<b>UL Recognized File #</b>	N/A
<b>UL Hazardous File #</b>	N/A
<b>CE</b>	None
<b>CSA File #</b>	N/A
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>