

68671 Cut Sheet



Viking machine tap, M8 X 1.00 UNF, high-speed steel (HSS), bright finish.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/68671>

Technical Specifications

Brand	Viking	Overall Length	2.8in (71mm)
Item	Machine tap	Tap Drill Size	7.0mm
Thread	M8 X 1.00 UNF	Material	High-speed steel (HSS)
Number of Flutes	2	Finish	Bright
Flute Style	Spiral flute	For Use On	Stainless steel, iron and steel
Tap Limit	D5	Application	Thread making

Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement