

68691 Cut Sheet

Viking machine tap, M12 X 1.25 UNF, high-speed steel (HSS), bright finish.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/68691>

Technical Specifications

Brand	Viking
Item	Machine tap
Thread	M12 X 1.25 UNF
Number of Flutes	3
Flute Style	Spiral flute
Tap Limit	D5

Overall Length	3.3in (84mm)
Tap Drill Size	10.8mm
Material	High-speed steel (HSS)
Finish	Bright
For Use On	Stainless steel, iron and steel
Application	Thread making

Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement