

# 69120068 Cut Sheet



WERMA FlatSIGN series LED signal column, (3) tiers, red/yellow/green, selectable permanent or blinking light function, (1) alarm, 115-230 VAC, clear lens, 194.9mm body length, transparent, 160 degree viewing angle, wall mount, IP65.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/69120068>

## Technical Specifications

<b>Brand</b>	WERMA
<b>Item</b>	Signal column
<b>Bulb Type</b>	LED
<b>Series</b>	FlatSIGN
<b>Number of Pre-Assembled Tiers</b>	3
<b>Light Color(s)</b>	Red/yellow/green
<b>Light Function</b>	Selectable permanent or blinking
<b>Number of Alarms</b>	1
<b>Voltage Rating</b>	115-230 VAC
<b>Lens Type</b>	Clear
<b>Body Length</b>	194.9mm

<b>Body Color</b>	Transparent
<b>Body Material</b>	ABS plastic
<b>Tower Viewing Angle</b>	160 degree
<b>Loudness Decibel</b>	80 dB at 1m
<b>Tone Frequency</b>	2.5 kHz
<b>Tone Type</b>	Continuous
<b>Touch to Acknowledge</b>	No
<b>Connector Type</b>	Pigtail
<b>Mounting</b>	Wall
<b>IP Rating</b>	IP65

## Agency Approvals

<b>UL Listed File #</b>	E164155
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/69120068.pdf>  
See store item page for other formats.