

69140068 Cut Sheet



WERMA FlatSIGN series LED signal column, (3) tiers, red/yellow/green, selectable permanent or blinking light function, (1) alarm, 115-230 VAC, clear lens, 194.9mm body length, silver, 160 degree viewing angle, wall mount, IP65.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/69140068>

Technical Specifications

Brand	WERMA
Item	Signal column
Bulb Type	LED
Series	FlatSIGN
Number of Pre-Assembled Tiers	3
Light Color(s)	Red/yellow/green
Light Function	Selectable permanent or blinking
Number of Alarms	1
Voltage Rating	115-230 VAC
Lens Type	Clear
Body Length	194.9mm

Body Color	Silver
Body Material	ABS plastic
Tower Viewing Angle	160 degree
Loudness Decibel	80 dB at 1m
Tone Frequency	2.5 kHz
Tone Type	Continuous
Touch to Acknowledge	No
Connector Type	Pigtail
Mounting	Wall
IP Rating	IP65

Agency Approvals

UL Listed File #	E164155
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/69140068.pdf>
See store item page for other formats.