

# 69150 Cut Sheet



Viking step drill bit, 3/16in to 7/8in, size #8, 12 steps, split point, high-speed steel (HSS), Titanium-Nitride (TiN) coated finish, 3/8in diameter 3-flat shank, 2.8in (71mm) overall length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/69150>

## Technical Specifications

|                      |                                                                                               |
|----------------------|-----------------------------------------------------------------------------------------------|
| Brand                | Viking                                                                                        |
| Item                 | Drill bit                                                                                     |
| Replacement          | No                                                                                            |
| Drill Bit Type       | Step                                                                                          |
| Size                 | 3/16in, 1/4in, 5/16in, 3/8in, 7/16in, 1/2in, 9/16in, 5/8in, 11/16in, 3/4in, 13/16in and 7/8in |
| Step Drill Size      | #8                                                                                            |
| Number Of Hole Sizes | 12                                                                                            |

|                |                                                                        |
|----------------|------------------------------------------------------------------------|
| Material       | High-speed steel (HSS)                                                 |
| Finish         | Titanium-Nitride (TiN) coated                                          |
| Point Cut      | Split                                                                  |
| Shank Type     | 3/8in diameter 3-flat                                                  |
| Overall Length | 2.8in (71mm)                                                           |
| For Use On     | Steel, brass, plastic, stainless steel, bronze, cast iron and aluminum |
| Application    | Hole cutting                                                           |

## Agency Approvals

|                      |                                                                     |
|----------------------|---------------------------------------------------------------------|
| UL Listed File #     | N/A                                                                 |
| UL Recognized File # | N/A                                                                 |
| UL Hazardous File #  | N/A                                                                 |
| CE                   | None                                                                |
| CSA File #           | N/A                                                                 |
| RoHS Status          | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH             | <a href="#">View EU REACH document</a>                              |
| Other                | <a href="#">RoHS Statement</a>                                      |