

# 69210 Cut Sheet



Viking step drill bit, 1/4in to 1-1/8in, size 1/4A, 16 steps, split point, high-speed steel (HSS), Titanium-Nitride (TiN) coated finish, 3/8in diameter 3-flat shank, 3.0in (76mm) overall length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/69210>

## Technical Specifications

<b>Brand</b>	Viking
<b>Item</b>	Drill bit
<b>Replacement</b>	No
<b>Drill Bit Type</b>	Step
<b>Size</b>	1/4in, 5/16in, 3/8in, 7/16in, 1/2in, 9/16in, 5/8in, 11/16in, 3/4in, 13/16in, 7/8in, 15/16in, 1in, 1-1/16in and 1-1/8in
<b>Step Drill Size</b>	1/4A
<b>Number Of Hole Sizes</b>	16

<b>Material</b>	High-speed steel (HSS)
<b>Finish</b>	Titanium-Nitride (TiN) coated
<b>Point Cut</b>	Split
<b>Shank Type</b>	3/8in diameter 3-flat
<b>Overall Length</b>	3.0in (76mm)
<b>For Use On</b>	Steel, brass, plastic, stainless steel, bronze, cast iron and aluminum
<b>Application</b>	Hole cutting

## Agency Approvals

<b>UL Listed File #</b>	N/A
<b>UL Recognized File #</b>	N/A
<b>UL Hazardous File #</b>	N/A
<b>CE</b>	None
<b>CSA File #</b>	N/A
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>