

# 69220 Cut Sheet



Viking step drill bit, 7/8in to 1-3/8in, size #12, 5 steps, split point, high-speed steel (HSS), Titanium-Nitride (TiN) coated finish, 3/8in diameter 3-flat shank, 2.8in (71mm) overall length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/69220>

## Technical Specifications

|                      |   |                |  |
|----------------------|---|----------------|--|
| Brand                | Viking  | Finish         | Titanium-Nitride (TiN) coated  |
| Item                 | Drill bit                                     | Point Cut      | Split  |
| Replacement          | No  | Shank Type     | 3/8in diameter 3-flat  |
| Drill Bit Type       | Step  | Overall Length | 2.8in (71mm)   |
| Size                 | 7/8in, 1-1/8in, 1-7/32in, 1-1/4in and 1-3/8in | For Use On     | Steel, brass, plastic, stainless steel, bronze, cast iron and aluminum |
| Step Drill Size      | #12   | Application    | Hole cutting   |
| Number Of Hole Sizes | 5   |                |  |
| Material             | High-speed steel (HSS)                        |                |  |

## Agency Approvals

|                      |   |
|----------------------|---|
| UL Listed File #     | N/A   |
| UL Recognized File # | N/A   |
| UL Hazardous File #  | N/A   |
| CE                   | None  |
| CSA File #           | N/A   |
| RoHS Status          | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH             | <a href="#">View EU REACH document</a>                              |
| Other                | <a href="#">RoHS Statement</a>                                      |