

69250 Cut Sheet



Viking step drill bit set, 3 pieces, high-speed steel (HSS), 3-flat shank, size #1, #3 and #4, imperial, Titanium-Nitride (TiN) coated finish, metal index case.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/69250>

Technical Specifications

Brand	Viking
Item	Drill bit set
Number of Pieces	3
Material	High-speed steel (HSS)
Drill Bit Type	Step
Drill Bit Size	1/8in, 5/32in, 3/16in, 7/32in, 1/4in, 9/32in, 5/16in, 11/32in, 3/8in, 13/32in, 7/16in, 15/32in, 1/2in, 9/16in, 5/8in, 11/16in and 3/4in
Step Drill Size	#1, #3 and #4
Number Of Hole Sizes	13, 6 and 9
Finish	Titanium-Nitride (TiN) coated
Point Cut	Split

Shank Type	3-flat
Application	Hole cutting
For Use On	Steel, brass, plastic, stainless steel, bronze, cast iron and aluminum
Measurement Type	Imperial
Package Type	Metal index case
Set Includes	Includes (1) #1 13 step drill bit (1/8in, 5/32in, 3/16in, 7/32in, 1/4in, 9/32in, 5/16in, 11/32in, 3/8in, 13/32in, 7/16in, 15/32in, 1/2in), (1) #4 6 step drill bit (3/16in, 1/4in, 5/16in, 3/8in, 7/16in, 1/2in), (1) #3 9 step drill bit (1/4in, 5/16in, 3/8in, 7/16in, 1/2in, 9/16in, 5/8in, 11/16in, 3/4in), plastic case

Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement