

# 6MJ-10MB Cut Sheet

HY-TECH hydraulic fluid adapter, straight, plated steel body, (1) -6 male JIC 37 deg and (1) -10 male o-ring boss. Package of 2.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/6MJ-10MB>

## Technical Specifications

Brand	HY-TECH
Item	Adapter
Working Fluid	Hydraulic fluid
Adapter Type	Straight
Body Material	Plated steel
Thread Material	Plated steel
Measurement Type	SAE
Connection	(1) -6 male JIC 37 deg and (1) -10 male o-ring boss
Quantity per Pack	2

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>