

# 7000-08351-0000000 Cut Sheet



Murrelektronik field wireable connector, M8 barrel 4-pin male axial connection, accepts cable diameter size 2.5-5.1mm, 22 - 26 AWG, insulation displacement (IDC) connection, IP67.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7000-08351-0000000>

## Technical Specifications

<b>Brand</b>	Murrelektronik
<b>Item</b>	Field wireable connector
<b>Connector Type</b>	M8 barrel 4-pin male axial connection
<b>Cable Diameter Size</b>	2.5-5.1mm
<b>Conductor Size</b>	22 - 26 AWG
<b>Terminal Connection</b>	Insulation displacement (IDC)
<b>Shielded</b>	No
<b>IP Rating</b>	IP67

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E224242
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>