

7000-08371-0000000 Cut Sheet



Murrelektronik field wireable connector, M8 nut 3-pin female axial connection, accepts cable diameter size 2.5-5.1mm, 22 - 26 AWG, insulation displacement (IDC) connection, IP67.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7000-08371-0000000>

Technical Specifications

Brand	Murrelektronik
Item	Field wireable connector
Connector Type	M8 nut 3-pin female axial connection
Cable Diameter Size	2.5-5.1mm
Conductor Size	22 - 26 AWG
Terminal Connection	Insulation displacement (IDC)
Shielded	No
IP Rating	IP67

Agency Approvals

UL Listed File #	None
UL Recognized File #	E224242
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement