


# 7000-08563-9690050 Cut Sheet



Murrelektronik bulkhead connector, M8 4-wire male to pigtail, 24 AWG, 1.6ft/0.5m cable length, nylon 12 conductor insulation material, IP67.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7000-08563-9690050>

## Technical Specifications

<b>Brand</b>	Murrelektronik
<b>Item</b>	Connector
<b>Form Factor</b>	Bulkhead
<b>Connection 1</b>	M8 male with male threads 4-wire/4-pin
<b>Connection 2</b>	Pigtail
<b>Shielded</b>	No

<b>Cable Length</b>	1.6ft/0.5m
<b>Conductor Size</b>	24 AWG
<b>Conductor Insulation Material</b>	Nylon 12
<b>Housing Material</b>	Nickel plated brass
<b>IP Rating</b>	IP67
<b>Includes</b>	Mounting nut(s)

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E224242
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/7000-08563-9690050.pdf>  
See store item page for other formats.