

# 7000-12021-2140500 Cut Sheet



Murrelektronik connection cable, M12 axial male A-coded to pigtail, 4-pole, 250 VAC/VDC, 4A, 22 AWG, PVC jacket, gray, unshielded, 16.4ft/5m cable length, IP65 IP66K IP67, sensor & signal.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7000-12021-2140500>

## Technical Specifications

|                 |                                          |
|-----------------|------------------------------------------|
| Brand           | Murrelektronik                           |
| Item            | Cable                                    |
| Cable Type      | Connection                               |
| Connection 1    | M12 axial male with male threads A-coded |
| Connection 2    | Pigtail                                  |
| Number of Poles | 4                                        |
| Voltage Rating  | 250 VAC/VDC                              |
| Amperage Rating | 4A                                       |

|                 |                 |
|-----------------|-----------------|
| Conductor Size  | 22 AWG          |
| Jacket Material | PVC             |
| Jacket Color    | Gray            |
| Shield Type     | Unshielded      |
| Cable Length    | 16.4ft/5m       |
| IP Rating       | IP65 IP66K IP67 |
| Application     | Sensor & signal |

## Agency Approvals

|                      |                                        |
|----------------------|----------------------------------------|
| UL Listed File #     | E325311                                |
| UL Recognized File # | n/a                                    |
| CE                   | <a href="#">View CE declarations</a>   |
| CSA File #           | 080128-0-000                           |
| RoHS Status          | Yes (See CE Doc)                       |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/7000-12021-2140500.pdf>  
See store item page for other formats.