7000-12221-2141500 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

Murrelektronik connection cable, M12 axial female to pigtail, 4-pole, PVC jacket, gray, 49.2ft/15m cable length, IP67, sensor & signal.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/7000-12221-2141500

Technical Specifications

Brand	Murrelektronik
Item	Cable
Cable Type	Connection
Connection 1	M12 axial female
Connection 2	Pigtail
Number of Poles	4
Jacket Material	PVC
Jacket Color	Gray
Cable Length	49.2ft/15m
IP Rating	IP67
Application	Sensor & signal

Agency Approvals

UL Listed File #	E325311
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	080128_0_000
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com
/static/drawings/7000-12221-2141500.pdf
See store item page for other formats.