

# 7000-12941-0000000 Cut Sheet



Murrelektronik connector, field-wireable, M12 nut 4-pin female axial connection, accepts cable diameter size 6-8mm, 18 AWG, screw terminal connection, IP67.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7000-12941-0000000>

## Technical Specifications

Brand	Murrelektronik
Item	Connector
Field-Wireable	Yes
Form Factor	Cable termination
Connector Type	M12
Coding	A-coded
Gender	Female with female threads
Angle	Axial

Number of Pins	4
Terminal Connection	Screw terminal
Cable Diameter Size	6-8mm
Conductor Size	18 AWG
Shielded	No
Housing Material	Polyamide
IP Rating	IP67

## Agency Approvals

UL Listed File #	None
UL Recognized File #	E224242
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	<a href="#">View EU REACH document</a>
Other	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/7000-12941-0000000.pdf>  
See store item page for other formats.