

7000-14581-0000000 Cut Sheet



Murrelektronik connector, field-wireable, M12 D-coded 4-pole male 90-degree, accepts cable diameter size 6-8mm, 18 AWG max, screw terminal connection, IP67.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7000-14581-0000000>

Technical Specifications

Brand	Murrelektronik
Item	Connector
Field-Wireable	Yes
Form Factor	Cable termination
Connector Type	M12
Coding	D-coded
Gender	Male with male threads
Angle	90-degree

Number of Pins	4
Terminal Connection	Screw terminal
Cable Diameter Size	6-8mm
Conductor Size	18 AWG max
Shielded	Yes
Housing Material	Die-cast zinc nickel-plated
IP Rating	IP67
Additional Information	Exceeds Category 5E specifications

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	1781018
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/7000-14581-0000000.pdf>
See store item page for other formats.