

7000-17121-2911000 Cut Sheet



Murrelektronik connection cable, M12 axial female to pigtail, 8-pole, PUR jacket, gray, shielded, 32.8ft/10m cable length, IP65 IP67.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7000-17121-2911000>

Technical Specifications

Brand	Murrelektronik
Item	Cable
Cable Type	Connection
Connection 1	M12 axial female
Connection 2	Pigtail
Number of Poles	8
Jacket Material	PUR
Jacket Color	Gray
Shield Type	Shielded
Cable Length	32.8ft/10m
IP Rating	IP65 IP67

Agency Approvals

UL Listed File #	E325311
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	1781018
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/7000-17121-2911000.pdf>
See store item page for other formats.