

# 7000-40621-2510100 Cut Sheet



Murrelektronik connection cable, M12 axial male A-coded to M8 right-angle female A-coded, 4-pole, 30 VAC/VDC, 4A, 24 AWG, PUR jacket, gray, unshielded, 3.2ft/1m cable length, IP65, IP66K and IP67, sensor & signal and drag chain.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7000-40621-2510100>

## Technical Specifications

|                        |   |
|------------------------|---|
| <b>Brand</b>           | Murrelektronik                                    |
| <b>Item</b>            | Cable   |
| <b>Cable Type</b>      | Connection  |
| <b>Connection 1</b>    | M12 axial male with male threads A-coded          |
| <b>Connection 2</b>    | M8 right-angle female with female threads A-coded |
| <b>Number of Poles</b> | 4   |
| <b>Voltage Rating</b>  | 30 VAC/VDC  |
| <b>Amperage Rating</b> | 4A  |

|                               |  |
|-------------------------------|--|
| <b>Conductor Size</b>         | 24 AWG   |
| <b>Jacket Material</b>        | PUR  |
| <b>Jacket Color</b>           | Gray   |
| <b>Shield Type</b>            | Unshielded                                     |
| <b>Cable Length</b>           | 3.2ft/1m                                       |
| <b>IP Rating</b>              | IP65, IP66K and IP67                           |
| <b>Application</b>            | Sensor & signal and drag chain                 |
| <b>Additional Information</b> | Suitable for drag chain and robot applications |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E325311                                |
| <b>UL Recognized File #</b> | N/A                                    |
| <b>UL Hazardous File #</b>  | N/A                                    |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | 080128-0-000                           |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/7000-40621-2510100.pdf>  
See store item page for other formats.