

7000-40621-2510500 Cut Sheet



Murrelektronik connection cable, M12 axial male A-coded to M8 right-angle female A-coded, 4-pole, 30 VAC/VDC, 4A, 24 AWG, PUR jacket, gray, unshielded, 16.4ft/5m cable length, IP65, IP66K and IP67, sensor & signal and drag chain.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7000-40621-2510500>

Technical Specifications

| | |
|------------------------|---|
| Brand | Murrelektronik |
| Item | Cable |
| Cable Type | Connection |
| Connection 1 | M12 axial male with male threads A-coded |
| Connection 2 | M8 right-angle female with female threads A-coded |
| Number of Poles | 4 |
| Voltage Rating | 30 VAC/VDC |
| Amperage Rating | 4A |

| | |
|-------------------------------|--|
| Conductor Size | 24 AWG |
| Jacket Material | PUR |
| Jacket Color | Gray |
| Shield Type | Unshielded |
| Cable Length | 16.4ft/5m |
| IP Rating | IP65, IP66K and IP67 |
| Application | Sensor & signal and drag chain |
| Additional Information | Suitable for drag chain and robot applications |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E325311 |
| UL Recognized File # | N/A |
| UL Hazardous File # | N/A |
| CE | View CE declarations |
| CSA File # | 080128-0-000 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/7000-40621-2510500.pdf>
See store item page for other formats.