

7000-74075-0000000 Cut Sheet



Murrelektronik field wireable connector, 8-pin RJ45 axial male heavy duty, accepts cable diameter size 5-9mm, 24-26 AWG, insulation displacement (IDC) connection, shielded, IP20. Use with Cat5 & Cat5e cable, transfer rate up to 1 Gbit/s.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7000-74075-0000000>

Technical Specifications

Brand	Murrelektronik
Item	Field wireable connector
Connector Type	8-pin RJ45 axial male heavy duty
Cable Diameter Size	5-9mm
Conductor Size	24-26 AWG
Terminal Connection	Insulation displacement (IDC)
Shielded	Yes
IP Rating	IP20
Additional Information	Use with Cat5 & Cat5e cable, transfer rate up to 1 Gbit/s

Agency Approvals

UL Listed File #	E362618
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement