

# 7000-88011-2110500 Cut Sheet



Murrelektronik connection cable, M8 axial male A-coded to M8 axial female A-coded, 4-pole, 50 VAC/60 VDC, 4A, 24 AWG, PVC jacket, gray, unshielded, 16.4ft/5m cable length, IP65 IP66K IP67 IP68, sensor & signal.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7000-88011-2110500>

## Technical Specifications

<b>Brand</b>	Murrelektronik
<b>Item</b>	Cable
<b>Cable Type</b>	Connection
<b>Connection 1</b>	M8 axial male with male threads A-coded
<b>Connection 2</b>	M8 axial female with female threads A-coded
<b>Number of Poles</b>	4
<b>Voltage Rating</b>	50 VAC/60 VDC
<b>Amperage Rating</b>	4A

<b>Conductor Size</b>	24 AWG
<b>Jacket Material</b>	PVC
<b>Jacket Color</b>	Gray
<b>Shield Type</b>	Unshielded
<b>Cable Length</b>	16.4ft/5m
<b>IP Rating</b>	IP65 IP66K IP67 IP68
<b>Application</b>	Sensor & signal

## Agency Approvals

<b>UL Listed File #</b>	E325311
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	080128-0-000
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/7000-88011-2110500.pdf>  
See store item page for other formats.