

7000-88011-2110500 Cut Sheet



Murrelektronik connection cable, M8 axial male A-coded to M8 axial female A-coded, 4-pole, 50 VAC/60 VDC, 4A, 24 AWG, PVC jacket, gray, unshielded, 16.4ft/5m cable length, IP65 IP66K IP67 IP68, sensor & signal.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7000-88011-2110500>

Technical Specifications

Brand	Murrelektronik
Item	Cable
Cable Type	Connection
Connection 1	M8 axial male with male threads A-coded
Connection 2	M8 axial female with female threads A-coded
Number of Poles	4
Voltage Rating	50 VAC/60 VDC
Amperage Rating	4A

Conductor Size	24 AWG
Jacket Material	PVC
Jacket Color	Gray
Shield Type	Unshielded
Cable Length	16.4ft/5m
IP Rating	IP65 IP66K IP67 IP68
Application	Sensor & signal

Agency Approvals

UL Listed File #	E325311
UL Recognized File #	n/a
CE	View CE declarations
CSA File #	080128-0-000
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/7000-88011-2110500.pdf>
See store item page for other formats.