

7000-P4541-P040200 Cut Sheet



Murrelektronik adapter cable, M12 axial female L-coded to 7/8in axial male, 5-pole, 63 VDC, 12A, 16 AWG, PUR jacket, black, 6.5ft/2m cable length, IP67.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7000-P4541-P040200>

Technical Specifications

Brand	Murrelektronik
Item	Cable
Cable Type	Adapter
Connection 1	M12 axial female L-coded
Connection 2	7/8in axial male
Number of Poles	5
Voltage Rating	63 VDC
Amperage Rating	12A
Conductor Size	16 AWG
Jacket Material	PUR
Jacket Color	Black
Cable Length	6.5ft/2m
IP Rating	IP67

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement