

7006180T Cut Sheet



KNIPEX diagonal cutters, 7.3in (184mm) overall length, insulated, 1000V insulation rating, induction hardened beveled cutting edges, insulated cushion grip handles, tether attachment point.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7006180T>

Technical Specifications

Brand	KNIPEX
Item	Cutters
Pliers Type	Diagonal
Overall Length	7.3in (184mm)
Insulated	Yes
Insulation Rating	1000V
Cutting	Induction hardened beveled cutting edges

Capacity	5/32in soft wire, 1/8in medium wire or 5/64in hard wire
Handle Type	Insulated cushion grip handles
Application	Wire cutting
Material	Vanadium steel, forged, multi-stage oil-hardened
Tool Features	Tether attachment point
Additional Information	VDE-tested

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement