

# 7008180SBA Cut Sheet

KNIPEX diagonal cutters, 7.3in (184mm) overall length, insulated, 1000V insulation rating, induction hardened beveled cutting edges, cushion grip handles.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7008180SBA>

## Technical Specifications

<b>Brand</b>	KNIPEX
<b>Item</b>	Cutters
<b>Pliers Type</b>	Diagonal
<b>Overall Length</b>	7.3in (184mm)
<b>Insulated</b>	Yes
<b>Insulation Rating</b>	1000V
<b>Cutting</b>	Induction hardened beveled cutting edges

<b>Capacity</b>	5/32in soft wire, 3/32in medium wire or 5/64in hard wire
<b>Handle Type</b>	Cushion grip handles
<b>Application</b>	Wire cutting
<b>Material</b>	Vanadium steel, forged, multi-stage oil-hardened
<b>Applicable Standards</b>	DIN ISO 5749
<b>Additional Information</b>	ASTM F1505-tested

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>