

7010001400U Cut Sheet



Metal Work manual valve, 3-port (3-way), 2-position, axial hand lever, detented, 1/8in female NPT inlet(s), 1/8in female NPT outlet(s), 1/8in female NPT exhaust(s), Cv=0.55.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7010001400U>

Technical Specifications

| | |
|----------------------------|----------------------------|
| Brand | Metal Work |
| Series | Series 70 |
| Item | Valve |
| Working Fluid | Air |
| Valve Type | Manual directional control |
| Port Quantity | 3-port (3-way) |
| Number Of Positions | 2 |
| Operator Type | Axial hand lever |
| Action | Detented |
| Body Material | Aluminum |

| | |
|-----------------------------------|------------------|
| Body Width | 22mm |
| Inlet Port | 1/8in female NPT |
| Outlet Port | 1/8in female NPT |
| Exhaust Port | 1/8in female NPT |
| Flow Coefficient | 0.55 |
| Maximum Operating Pressure | 145 psi (10 bar) |
| Minimum Operating Pressure | Vacuum |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/7010001400U.pdf>
See store item page for other formats.