

7010020400U Cut Sheet



Metal Work solenoid valve, 3-port (3-way), 2-position, N.O., single solenoid spring return, 1/8in female NPT inlet(s), 1/8in female NPT outlet(s), 1/8in female NPT exhaust(s), Cv=0.55.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7010020400U>

Technical Specifications

Brand	Metal Work	Inlet Port	1/8in female NPT
Item	Valve	Outlet Port	1/8in female NPT
Working Fluid	Pneumatic	Exhaust Port	1/8in female NPT
Valve Type	Solenoid directional control	Manual Override Type	Locking
Port Quantity	3-port (3-way)	Flow Coefficient	0.55
Number Of Positions	2	Maximum Operating Pressure	145 psi (10 bar)
Valve Configuration	N.O.	Minimum Operating Pressure	37 psi (2.5 bar)
Action	Single solenoid spring return	Additional Information	Purchase solenoid coil in desired voltage separately
Body Material	Aluminum		
Body Width	22mm		

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/7010020400U.pdf>
See store item page for other formats.