

7020000600U Cut Sheet



Metal Work pneumatic manual valve, 5-port (4-way), 3-position, center exhaust, 90 deg hand lever, detented, 1/4in female NPT inlet(s), 1/4in female NPT outlet(s), 1/4in female NPT exhaust(s), Cv=1.1.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7020000600U>

Technical Specifications

Brand	Metal Work
Item	Valve
Working Fluid	Air or inert gas
Valve Type	Manual directional control
Series	Series 70
Port Quantity	5-port (4-way)
Number Of Positions	3
Valve Configuration	Center exhaust
Operator Type	90 deg hand lever
Action	Detented

Body Material	Aluminum
Body Width	25mm
Inlet Port	1/4in female NPT
Outlet Port	1/4in female NPT
Exhaust Port	1/4in female NPT
Flow Coefficient	1.1
Maximum Operating Pressure	145 psi (10 bar)
Minimum Operating Pressure	Vacuum

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/7020000600U.pdf>
See store item page for other formats.