


7024-12241-3391000 Cut Sheet



Murrelektronik connection cable, M12 axial female to pigtail, 5-pole, styrene-butadiene thermoplastic (TPE-S) jacket, ice blue, 32.8ft/10m cable length, IP65, IP68 and IP69K, suitable for food and beverage applications, FDA compliant.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7024-12241-3391000>

Technical Specifications

Brand	Murrelektronik
Item	Cable
Cable Type	Connection
Connection 1	M12 axial female
Connection 2	Pigtail
Number of Poles	5
Jacket Material	Styrene-butadiene thermoplastic (TPE-S)
Jacket Color	Ice blue
Cable Length	32.8ft/10m
IP Rating	IP65, IP68 and IP69K
Application	Suitable for food and beverage applications, FDA compliant

Agency Approvals

UL Listed File #	E325311
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	080128_0_000
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/7024-12241-3391000.pdf>
See store item page for other formats.