

# 70615NC Cut Sheet



Bryant industrial heavy duty locking blade connector, 15A, 250 VAC, 1-phase, 2-pole, 3-wire, NEMA L6-15, accepts cord size 0.3-0.65in, nylon housing, black and white.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/70615NC>

## Technical Specifications

Brand	Bryant
Item	Connector
Application	Industrial heavy duty
Blade Type	Locking
With Cap	No
Self-grounding	No
Amperage Rating	15A
Voltage Rating	250 VAC
Number of Phases	1
Number of Poles	2
Number of Wires	3
Wire Size	18-8 AWG
Copper Wire Only	No
Configuration	NEMA L6-15
Cord Diameter	0.3-0.65in
Housing Material	Nylon
Color	Black and white

## Agency Approvals

UL Listed File #	E1381
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	016215
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>