

70720NC Cut Sheet



Bryant industrial heavy duty locking blade connector, 20A, 277 VAC, 1-phase, 2-pole, 3-wire, NEMA L7-20, accepts cord size 0.3-0.95in, nylon housing, black and white.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/70720NC>

Technical Specifications

Brand	Bryant
Item	Connector
Application	Industrial heavy duty
Blade Type	Locking
With Cap	No
Self-grounding	No
Amperage Rating	20A
Voltage Rating	277 VAC
Number of Phases	1

Number of Poles	2
Number of Wires	3
Wire Size	18-8 AWG
Copper Wire Only	No
Configuration	NEMA L7-20
Cord Diameter	0.3-0.95in
Housing Material	Nylon
Color	Black and white

Agency Approvals

UL Listed File #	E1381
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	016215
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/70720NC.pdf>
See store item page for other formats.