

70730NC Cut Sheet



Bryant industrial heavy duty locking blade connector, 30A, 277 VAC, 1-phase, 2-pole, 3-wire, NEMA L7-30, accepts cord size 0.3-0.95in, nylon housing, black and white.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/70730NC>

Technical Specifications

| | |
|-------------------------|-----------------------|
| Brand | Bryant |
| Item | Connector |
| Application | Industrial heavy duty |
| Blade Type | Locking |
| With Cap | No |
| Self-grounding | No |
| Amperage Rating | 30A |
| Voltage Rating | 277 VAC |
| Number of Phases | 1 |
| Number of Poles | 2 |
| Number of Wires | 3 |
| Wire Size | 18-8 AWG |
| Copper Wire Only | No |
| Configuration | NEMA L7-30 |
| Cord Diameter | 0.3-0.95in |
| Housing Material | Nylon |
| Color | Black and white |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E1381 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | 016215 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |