

7101160SBA Cut Sheet



KNIPEX CoBolt bolt cutters, 6.3in (159mm) overall length, induction hardened centered cutting edges, plastic coated handles, lever action cutting.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7101160SBA>

Technical Specifications

Brand	KNIPEX
Series	CoBolt
Item	Bolt cutters
Overall Length	6.3in (159mm)
Insulated	No
Cutting	Induction hardened centered cutting edges
Capacity	13/64in soft wire, 11/64in medium wire or 1/8in hard wire

Handle Type	Plastic coated handles
Application	Bolt cutting, gripping and pulling
Material	Chrome vanadium heavy-duty steel, forged, oil-hardened
Tool Features	Lever action cutting
Additional Information	Cuts materials like bolts, nails, rivets, etc. up to 13/64in diameter

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement