

7101200SBA Cut Sheet



KNIPEX CoBolt bolt cutters, 8.0in (203mm) overall length, induction hardened centered cutting edges, multi-component soft grip handle, lever action cutting.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7101200SBA>

Technical Specifications

Brand	KNIPEX
Series	CoBolt
Item	Bolt cutters
Overall Length	8.0in (203mm)
Insulated	No
Cutting	Induction hardened centered cutting edges
Capacity	1/4in soft wire, 13/64in medium wire or 5/32in hard wire

Handle Type	Multi-component soft grip handle
Application	Bolt cutting, gripping and pulling
Material	Chrome vanadium heavy-duty steel, forged, oil-hardened
Tool Features	Lever action cutting
Additional Information	Cuts materials like bolts, nails, rivets, etc. up to 1/4in diameter

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document