

7101250SBA Cut Sheet



KNIPEX CoBolt bolt cutters, 10.0in (254mm) overall length, induction hardened centered cutting edges, plastic coated handles, lever action cutting.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7101250SBA>

Technical Specifications

Brand	KNIPEX	Handle Type	Plastic coated handles
Series	CoBolt	Application	Bolt cutting, gripping and pulling
Item	Bolt cutters	Material	Chrome vanadium heavy-duty steel, forged, oil-hardened
Overall Length	10.0in (254mm)	Tool Features	Lever action cutting
Insulated	No	Additional Information	Cuts materials like bolts, nails, rivets, etc. up to 7/32in diameter
Cutting	Induction hardened centered cutting edges		
Capacity	7/32in medium wire or 5/32in hard wire		

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement