

7111HV Cut Sheet



Trumeter electrical counter, 9mm 8-digit LCD, 5-110 VDC or 10-240 VAC input, remote, manual or disabled reset, rectangular flush mount with clip, screw terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7111HV>

Technical Specifications

Brand	Trumeter
Item	Counter
Counter Type	Electrical
Count Direction	Up/down
Count Speed	10Hz
Display Type	LCD
Display Size	9mm 8-digit
Reset	Remote, manual or disabled
Input Signal	5-110 VDC or 10-240 VAC
Mounting	Panel
Mounting Type	Rectangular flush mount with clip

Mounting Hole Size	1/32 DIN
Connector Type	Screw terminals
Includes	NEMA 4X gasket
Additional Information	5-30 VDC externally powered backlight, requires separate resistor above 5 VDC
Dangerous Goods	<ul style="list-style-type: none">• Battery Installed: Yes• Packaging Instructions: 970• UN Number: UN3091• Hazard Type: Lithium Battery• Battery Type: Other• Generic Battery: CR2477

Agency Approvals

UL Listed File #	None
UL Recognized File #	E36690
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/7111HV.pdf>
See store item page for other formats.